

Datasheet

DPYSL4 polyclonal antibody (A01)

Catalog Number: H00010570-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant DPYSL4.

Immunogen: DPYSL4 (NP_006417, 461 a.a. ~ 559 a.a) partial recombinant protein with GST tag.

Sequence:

VTPGAGRFVPRKTFPDFVYKRIKARNRLAEIHGVPRGL
YDGPVHEVMVPAKPGSGAPARASCPGKISVPPVRNLH
QSGFSLSGSQADDHIARRTAQKIM

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Ce, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10570

Gene Symbol: DPYSL4

Gene Alias: CRMP3, DRP-4, ULIP4

References:

1. Identification of dihydropyrimidinase-related protein 4 as a novel target of the p53 tumor suppressor in the apoptotic response to DNA damage. Kimura J, Kudoh T, Miki Y, Yoshida K. Int J Cancer. 2011 Apr 1;128(7):1524-31. doi: 10.1002/ijc.25475. Epub 2010 May 24.