

Datasheet

KIF20A polyclonal antibody

Gene Alias: FLJ21151, MKLP2, RAB6KIFL

Catalog Number: PAB25094

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of KIF20A.

Immunogen: A synthetic peptide corresponding to KIF20A.

Host: Rabbit

Theoretical MW (kDa): 100

Reactivity: Human

Applications: IF, IHC-P, WB-Ce
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: KIF20A polyclonal antibody detects endogenous levels of KIF20A protein.

Form: Liquid

Purification: Affinity purification

Concentration: 1 mg/mL

Recommend Usage: Western Blot (1:500-1:1000)
Immunohistochemistry (1:50-1:200)
Immunofluorescence (1:50-1:200)
The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.2 (0.05% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10112

Gene Symbol: KIF20A