

Datasheet

GNL3 monoclonal antibody (M08), clone 1G4

Catalog Number: H00026354-M08

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a full length recombinant GNL3.

Clone Name: 1G4

Immunogen: GNL3 (AAH01024.1, 328 a.a. ~ 427 a.a)
full-length recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

IEVVKPMEAASAILSQADARQVVLKYTVPGYRNSLEFF
TMLAQRRGMHQKGGIPNVEGAALKLWSEWTGASLAY
YCHPPTSWTPPPYFNESIVVDMKSGF

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re, WB-Tr
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 26354

Gene Symbol: GNL3

Gene Alias: C77032, E2IG3, MGC800, NS