9F, No. 108, Jhouzih St., Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

GNL3 monoclonal antibody (M09), clone 4B10

Catalog Number: H00026354-M09

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a full length recombinant GNL3.

Clone Name: 4B10

Immunogen: GNL3 (AAH01024.1, 328 a.a. ~ 427 a.a) full-length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:
IEVVKPMEAASAILSQADARQVVLKYTVPGYRNSLEFF
TMLAQRRGMHQKGGIPNVEGAAKLLWSEWTGASLAY
YCHPPTSWTPPPYFNESIVVDMKSGF

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 26354

Gene Symbol: GNL3

Gene Alias: C77032, E2IG3, MGC800, NS