

Datasheet

LHX6 polyclonal antibody (A01)

biological validity has not been determined. [provided by RefSeq]

Catalog Number: H00026468-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant LHX6.

Immunogen: LHX6 (NP_055183, 274 a.a. ~ 363 a.a) partial recombinant protein with GST tag.

Sequence:

HKKHTPQHVPVPSGAPPSRLPSALSDDIHYTPFSSPE
RARMVTLHGYIESQVQCGQVHCRLPYTAPPVHLKAD
MDGPLSNRGEKVILFQY

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 26468

Gene Symbol: LHX6

Gene Alias: LHX6.1, MGC119542, MGC119544, MGC119545

Gene Summary: This gene encodes a member of a large protein family that contains the LIM domain, a unique cysteine-rich zinc-binding domain. The encoded protein may function as a transcriptional regulator and may be involved in the control of differentiation and development of neural and lymphoid cells. Two alternatively spliced transcript variants encoding distinct isoforms have been described for this gene. Alternatively spliced transcript variants have been identified, but their